





Position of the shower cubicle





Left and right sides summed must not exceed 385 mm.







PACKAGE CODES (See marks on page 4)

REP	VERSION	100 x 70	100 x 80	100 x 90	120 x 70	120 x 80	120 x 90	140 x 70	140 x 80	140 x 90	160 x 70	160 x 80	160 x 90	170 x 70	170 x 80	170 x 90
A		REC561	REC562	REC563	REC564	REC565	REC566	REC567	REC568	REC569	REC570	REC571	REC572	REC573	REC574	REC575
B		C11444E	C11445E	C11446E	C11444E	C11445E	C11446E	C11444E	C11445E	C11446E	C11444E	C11445E	C11446E	C11444E	C11445E	C11446E
C		C11439E			C11431E											
D					C11440E			C11441E			C11442E			C11443E		
E		C11354E	C11355E	C11356E	C11354E	C11355E	C11356E	C11354E	C11355E	C11356E	C11354E	C11355E	C11356E	C11354E	C11355E	C11356E
F	SER	C11374E			C11375E			C11376E			C11377E			C11378E		
	TN	C11369E			C11370E			C11371E			C11372E			C11373E		
G	SER	C11394E			C11395E			C11396E			C11397E			C11398E		
	TN	C11389E			C11390E			C11391E			C11392E			C11393E		


























(SK) Left hand x1 SUP172	(SL) Right hand x1 SUP173	(PS) x2 PPL1116
(SC) Left hand x1 SUP164	(SD) Right han x1 SUP165	(PT) 120/140/160/170 x1 100 x0 PPL1117
(PG) Left hand x1 PPL1102	(PH) Right hand x1 PPL1103	(MA) x1 MIT100
(PAB) Left hand x1 PPL1134	(PAC) Right hand x1 PPL1135	(MB) x1 MIT94
(PAX) x4 PPL1318	(VG) x2 SET03	





1














PA 120/140/160/170x11 100x9  PPL802	PB 120/140/160/170x11 100x9  PPL804	QA x1  BOND28												
TA x1  TOL11	VN Ø4 x11  45 1=1 VIS231													
VA x11  CHE02	VV x11  RON34	AU x2  Lg=1940mm 6210-01												
AA x1  Lg=1972mm 6189-01	AS x1  <table><tr><th colspan="2">6209 Length</th></tr><tr><td>100</td><td>Lg=950mm</td></tr><tr><td>120</td><td>Lg=1150mm</td></tr><tr><td>140</td><td>Lg=1350mm</td></tr><tr><td>160</td><td>Lg=1550mm</td></tr><tr><td>170</td><td>Lg=1650mm</td></tr></table>		6209 Length		100	Lg=950mm	120	Lg=1150mm	140	Lg=1350mm	160	Lg=1550mm	170	Lg=1650mm
6209 Length														
100	Lg=950mm													
120	Lg=1150mm													
140	Lg=1350mm													
160	Lg=1550mm													
170	Lg=1650mm													
AB 120/140/160/170x1 100x0  Lg=1972mm 6190-01	AT x1  <table><tr><th colspan="2">6209 Width</th></tr><tr><td>70</td><td>Lg=635mm</td></tr><tr><td>80</td><td>Lg=735mm</td></tr><tr><td>90</td><td>Lg=835mm</td></tr></table>		6209 Width		70	Lg=635mm	80	Lg=735mm	90	Lg=835mm				
6209 Width														
70	Lg=635mm													
80	Lg=735mm													
90	Lg=835mm													

2


TE 120/140/160/170 x6 100 x4  TOL102	TF 120/140/160/170 x6 100 x4  TOL103	PAA 120/140/160/170 x5 100 x4  PPL1133
JG 120/140/160/170 x6 100 x4  Lg=1971mm P101	VQ 120/140/160/170 x5 100 x4  1=1 VIS238	VR 120/140/160/170 x6 100 x4  1=1 VIS239
PAL 120/140/160/170 x1 100 x0  PPL1128	AA x1  Lg=1972mm 6189-01	VD x3  SET88
QB 120/140/160/170 x2 100 x3  BOU40		



4

SA Left hand x1  SET107	SB Right hand x1  SET108	VM Ø3.5 x8  1=1 VIS215
PI Left hand x1  PPL1104	PJ Right hand x1  PPL1105	PAA x1  PPL1133
SI Left hand x1  SUP170	SJ Right hand x1  SUP171	JG x1  Lg=1971mm P101
PK Left hand x1  PPL1106	PL Right hand x1  PPL1107	QC x1  BUT22
VP Ø3.5 x3  1=1 VIS237		

AG




x1

6196
Length

100	Lg=880mm
120	Lg=1080mm
140	Lg=1280mm
160	Lg=1480mm
170	Lg=1580mm

AD



x1

6194
Length

100	Lg=456mm
120	Lg=556mm
140	Lg=656mm
160	Lg=756mm
170	Lg=806mm

AJ



x1

6199
Length

100	Lg=401mm
120	Lg=501mm
140	Lg=601mm
160	Lg=701mm
170	Lg=751mm

AQ















x2
















Lg=300mm

6206-01


5


(JE) x1  Lg=820mm JOI239	(PC) x1  PPL823	(JC) x1  Lg=1882mm J723
(PAR) x1  PPL1136/1137	(JB) x1  Lg=1959mm AI150	(VM) Ø3.5 x1  19 1=1 VIS215
(PO) Left hand x1  PPL1110	(PP) Right hand x1  PPL1111	(QE) 140/160/170 x3 100/120 x2  ROU37
(PD) x1  PPL1080	(PE) x1  PPL1081	(JA) x1  AIM36
(JD) x1  Lg=1894mm J719	(QD) x1  PGN36	

6


VQ Ø4.2 x6  1=1 VIS238	PF 140/160/170 100/120 x4 x3  PPL1099	VO Ø3.5 x9  1=1 VIS253
PAK 140/160/170 100/120 x5 x3  SET105	VI x3  Lg=2800mm VEL06-5	VJ x3  Lg=2800mm VEL06-6
SG Left hand x1  SUP168	SH Right hand x1  SUP169	JJ x2  Lg=2200mm PFL84
AE x1  Lg=2030mm 6195-01	FA x1  2055 125 PUS132	FC x1  2000 472 PUS134
AH x2  Lg=1998mm 6197-01		

Tools required







1B



1C






2


2

2B




2


2C




3




4



5



6



7

